



Taylor #1442 Critical Care Digital Thermometer For Monitoring Temperature-Critical Materials

Temperature Range:

-40F to 392F

-40C to 200C

Resolution:

.1F or .1C

Accuracy:

20F to 212F + or - 1.8F

-40F to 19F + or - 3.6F

213F to 392F+ or - 3.6F



- Dual 6' glycol-tolerant probes
- Programmable high and low limit audible alarms
- Each probe operates independently
- Password protected for operational security
- Moisture resistant case
- 96-hour memory of high and low temperatures
- 96-hour memory also records history of alarm breaches including time and duration
- C – F switch-able
- LCD size 1.375" x 3" Digit size .5"
- LCD idle to preserve battery life
- Tamperproof construction
- Membrane switch operation
- Exterior Velcro mount for smooth surfaces
- Operates on two (2) AAA batteries (included)
- 12-month Limited Warranty